

Plastic box for manifolds art. AC 850



The modular inspection box AC 850 for 1" or 3/4" manifolds is suitable to house brass bar, modular or coplanar manifolds. Handy to store and transport, it is easy to mount and extremely capacious once assembled. It is supplied with all the screws, supports and accessories required for installation. Available in four sizes.


■ TECHNICAL FEATURES

Temperature range: 0÷70 °C

■ MATERIALS

Case and cover: shockproof polystyrene
Inner supports: PP

■ DIMENSIONS



ART.	COD.	A	B	C	D	E	F
AC 850	SAM-032	272	332	86	290	350	15
AC 850	SAM-040	272	412	86	290	430	15
AC 850	SAM-050	272	512	86	290	530	15
AC 850	SAM-060	272	612	86	290	630	15


Note: effective inner dimensions of the boxes are:

- Short side [mm]: 260;
- Width [mm]: 95;
- Long side [mm]: see table below


SAM-032	SAM-040	SAM-050	SAM-060
320	400	500	600

■ OPERATING INSTRUCTIONS


AC 850 boxes can house brass bar (Fig.1a), coplanar (Fig.1b) or modular (Fig.1c and Fig.1d) manifolds. Please refer to the reported instructions for a correct installation.




(a) Bar manifold installation.



(b) Coplanar manifold installation.



(c) Modular manifold CI 300NB/NR installation.



(d) Modular manifold EASY-LOCK installation.

Fig. 1: Installation instructions to house different types of manifolds in the box. A = plastering protection.

I.V.A.R. S.p.A.
Via IV Novembre 181
25080 Prevalle (BS)
Tel. +39 030 68028
Fax +39 030 6801329
www.ivar.eu - info@ivar.eu

I.V.A.R. S.p.A. reserves the right to make enhancements and changes to products and relative documentation at any time without prior notice. All rights reserved. Reproduction, even partial, is forbidden without prior permission by the copyright owner.